




Woven stainless steel wire cloth

Opening size: from 0.026mm to 20mm
Weaving type: Plain and twill
Steel grade (material): AISI 304

Plain weave**Twill** weave

Main application:

for screening; separation of particles; filtration process of liquids, solutions, melts, mixtures etc.; as a part of equipment operated in aggressive conditions and high and low temperatures; gas filtration; air cleaning.

Woven stainless steel wire cloth

Plain and twill wire cloth

	Wielkość oczka mm	Średnica drutu mm	Procent otwartej powierzchni %
Wire cloth 0,026x0,025 stainless steel	0,026	0,025	26
Wire cloth 0,03x0,025 stainless steel	0,03	0,025	30
Wire cloth 0,04x0,03 stainless steel	0,04	0,03	33
Wire cloth 0,04x0,035 stainless steel	0,04	0,035	28
Wire cloth 0,05x0,035 stainless steel	0,05	0,035	35
Wire cloth 0,063x0,032 stainless steel	0,063	0,032	44
Wire cloth 0,063x0,04 stainless steel	0,063	0,04	37
Wire cloth 0,071x0,055 stainless steel	0,071	0,055	32
Wire cloth 0,071x0,056 stainless steel	0,071	0,056	31
Wire cloth 0,075x0,05 stainless steel	0,075	0,05	36
Wire cloth 0,08x0,04 stainless steel	0,08	0,04	44
Wire cloth 0,08x0,055 stainless steel	0,08	0,055	35
Wire cloth 0,08x0,055x1300 stainless steel	0,08	0,055	35
Wire cloth 0,09x0,05 stainless steel	0,09	0,05	41
Wire cloth 0,094x0,055 stainless steel	0,094	0,055	40
Wire cloth 0,1x0,05 stainless steel	0,1	0,05	44
Wire cloth 0,1x0,063 stainless steel	0,1	0,063	38
Wire cloth 0,125x0,08 stainless steel	0,125	0,08	37
Wire cloth 0,14x0,09 stainless steel	0,14	0,09	37
Wire cloth 0,14x0,1 stainless steel	0,14	0,1	34
Wire cloth 0,14x0,11 stainless steel	0,14	0,11	31
Wire cloth 0,16x0,1x1300 stainless steel	0,16	0,1	38
Wire cloth 0,16x0,12 stainless steel	0,16	0,12	33
Wire cloth 0,17x0,12 stainless steel	0,17	0,12	34
Wire cloth 0,18x0,12 stainless steel	0,18	0,12	36
Wire cloth 0,2x0,12x1300 stainless steel	0,2	0,12	39
Wire cloth 0,2x0,13 stainless steel	0,2	0,13	37
Wire cloth 0,2x0,13x1500 stainless steel	0,2	0,13	37
Wire cloth 0,2x0,15 stainless steel	0,2	0,15	33
Wire cloth 0,25x0,16x1300 stainless steel	0,25	0,16	37
Wire cloth 0,25x0,16 stainless steel	0,25	0,16	37
Wire cloth 0,25x0,2 stainless steel	0,25	0,2	31

Wire cloth 0,25x0,2x1200 stainless steel	0,25	0,2	31
Wire cloth 0,3x0,12 stainless steel	0,3	0,12	51
Wire cloth 0,3x0,2 stainless steel	0,3	0,2	36
Wire cloth 0,315x0,16 stainless steel	0,315	0,16	44
Wire cloth 0,4x0,15 stainless steel	0,4	0,15	53
Wire cloth 0,4x0,16 stainless steel	0,4	0,16	51
Wire cloth 0,4x0,2 stainless steel	0,4	0,2	44
Wire cloth 0,4x0,2x1300 stainless steel	0,4	0,2	44
Wire cloth 0,4x0,25 stainless steel	0,4	0,25	38
Wire cloth 0,5x0,2 stainless steel	0,5	0,2	51
Wire cloth 0,5x0,25 stainless steel	0,5	0,25	44
Wire cloth 0,5x0,3 stainless steel	0,5	0,3	39
Wire cloth 0,55x0,16 stainless steel	0,55	0,16	60
Wire cloth 0,6x0,16 stainless steel	0,6	0,16	62
Wire cloth 0,63x0,25 stainless steel	0,63	0,25	51
Wire cloth 0,63x0,32 stainless steel	0,63	0,32	44
Wire cloth 0,63x0,4 stainless steel	0,63	0,4	37
Wire cloth 0,63x0,4x1500 stainless steel	0,63	0,4	37
Wire cloth 0,7x0,22 stainless steel	0,7	0,22	58
Wire cloth 0,7x0,25 stainless steel	0,7	0,25	54
Wire cloth 0,7x0,28 stainless steel	0,7	0,28	51
Wire cloth 0,7x0,32 stainless steel	0,7	0,32	47
Wire cloth 0,8x0,2 stainless steel	0,8	0,2	64
Wire cloth 0,8x0,25 stainless steel	0,8	0,25	58
Wire cloth 0,8x0,32 stainless steel	0,8	0,32	51
Wire cloth 0,8x0,4 stainless steel	0,8	0,4	44
Wire cloth 0,9x0,22 stainless steel	0,9	0,22	65
Wire cloth 0,9x0,36 stainless steel	0,9	0,36	51
Wire cloth 1x0,16 stainless steel	1	0,16	74
Wire cloth 1x0,22 stainless steel	1	0,22	67
Wire cloth 1x0,22x1500 stainless steel	1	0,22	67
Wire cloth 1x0,25 stainless steel	1	0,25	64
Wire cloth 1x0,3 stainless steel	1	0,3	59
Wire cloth 1x0,32 stainless steel	1	0,32	57

Wire cloth 1x0,4 stainless steel	1	0,4	51
Wire cloth 1x0,5 stainless steel	1	0,5	44
Wire cloth 1x0,6 stainless steel	1	0,6	39
Wire cloth 1,2x0,22x1500 stainless steel	1,2	0,22	71
Wire cloth 1,2x0,32 stainless steel	1,2	0,32	62
Wire cloth 1,2x0,4 stainless steel	1,2	0,4	56
Wire cloth 1,2x0,6 stainless steel	1,2	0,6	44
Wire cloth 1,25x0,5 stainless steel	1,25	0,5	51
Wire cloth 1,25x0,7 stainless steel	1,25	0,7	41
Wire cloth 1,25x0,8 stainless steel	1,25	0,8	37
Wire cloth 1,4x0,36 stainless steel	1,4	0,36	63
Wire cloth 1,5x0,5 stainless steel	1,5	0,5	56
Wire cloth 1,6x0,4 stainless steel	1,6	0,4	64
Wire cloth 1,6x0,8 stainless steel	1,6	0,8	44
Wire cloth 1,8x0,7 stainless steel	1,8	0,7	52
Wire cloth 2x0,4 stainless steel	2	0,4	69
Wire cloth 2x0,5 stainless steel	2	0,5	64
Wire cloth 2x0,6 stainless steel	2	0,6	59
Wire mesh 2x0,7 stainless steel	2	0,7	55
Wire mesh 2x0,8 stainless steel	2	0,8	51
Wire mesh 2x1 stainless steel	2	1	44
Wire cloth 2,2x0,45 stainless steel	2,2	0,45	69
Wire cloth 2,2x0,7 stainless steel	2,2	0,7	58
Wire cloth 2,5x0,4 stainless steel	2,5	0,4	74
Wire cloth 2,5x0,5 stainless steel	2,5	0,5	69
Wire cloth 2,5x0,6 stainless steel	2,5	0,6	65
Wire mesh 2,5x1 stainless steel	2,5	1	51
Wire cloth 3x0,5 stainless steel	3	0,5	73
Wire mesh 3x1 stainless steel	3	1	56
Wire cloth 3,2x0,5 stainless steel	3,2	0,5	75
Wire cloth 3,2x0,8 stainless steel	3,2	0,8	64
Wire mesh 3,2x1,2 stainless steel	3,2	1,2	53
Wire cloth 3,5x0,7 stainless steel	3,5	0,7	69
Wire mesh 3,5x1 stainless steel	3,5	1	60

Wire mesh 4x0,6 stainless steel	4	0,6	76
Wire mesh 4x1 stainless steel	4	1	64
Wire mesh 4x1,2 stainless steel	4	1,2	59
Wire mesh 5x0,7 stainless steel	5	0,7	77
Wire mesh 5x1 stainless steel	5	1	69
Wire mesh 5x1,2 stainless steel	5	1,2	65
Wire mesh 5x1,6 stainless steel	5	1,6	57
Wire mesh 5x2 stainless steel	5	2	51
Wire mesh 6x1,2 stainless steel	6	1,2	69
Wire mesh 6x2 stainless steel	6	2	56

Delivery form: Woven wire mesh is available in rolls, and it is possible to unwind the required quantity from a roll.

